## Microtomy and Histology

## Please scroll to bottom of page

## **Heated Forceps/Tweezers**

These Premier Heated Forceps are designed for paraffin embedding to reduce the "carry-over" often associated with ordinary forceps. The system has been designed with dual outlet control box to accept two pairs of forceps with a choice of tip sizes of 1mm, 2mm and 4mm. The tip temperature remains constant and is supplied from a safe 12v power supply.

**F318** Dual outlet control box with transformer

F320 Forceps 15cm x 1mm tip (red)
F321 Forceps 15cm x 4mm tip (blue)
F322 Forceps 15cm x 2mm tip (yellow)



## **Slide Dryer and Hybridisation Hotplate**

Two units with black non-reflecting surfaces for excellent section visualisation, variable temperature control, uniform surface temperature, accuracy ±1°C with digital display.

H069 Slide dryer 150 x 555 x 75mm 220/240v 50-60Hz, 110v/A, range room temper-

ature to 85°C, weight 4Kg

Hybridisation unit dimensions, power supply, weight as above, range room

temperature to 100°C.



E-mail: sales@taab.co.uk

12.3